





















ASATHIOSOL COLOURS (1)		Dyeing depth (g/L)	Fastness				
Dyeing Colour Sample	Product Name		Light	Washing			Rubbing (Dry)
				Shade Change	Staining		
			on Cotton		on Rayon		
	Asathiosol Yellow S-GG 50%	50	3	5	5	5	4
	Asathiosol Yellow S-RR 50%	50	3	5	5	5	4
	Asathiosol Orange S-2R	25	3	5	5	5	4
	Asathiosol Brown S-GN	50	5	5	5	5	4
	Asathiosol Brown S-RF	50	5-6	5	5	5	4
	Asathiosol Brown S-BR	50	4-5	5	5	5	4
	Asathiosol Bordeaux S-3B	25	4	4-5	4	4-5	3-4
	Asathiosol Red Brown S-RT	50	4-5	4	4	4-5	4
	Asathiosol Red Brown S-6B	50	3-4	5	5	5	4-5
	Asathiosol Black Brown S-RD	50	4-5	5	5	5	4

Fastness Light : JIS L-0842 (Carbon arc lamp)

ASATHIOSOL COLOURS (2)		Dyeing depth (g/L)	Fastness				
Dyeing Colour Sample	Product Name		Light	Washing			Rubbing (Dry)
				Shade Change	Staining		
			on Cotton		on Rayon		
	Asathiosol Olive S-KD	50	4-5	5	4-5	5	4
	Asathiosol Olive S-BB	50	4-5	4-5	4-5	5	4
	Asathiosol Brilliant Green S-GO	25	4-5	4-5	4-5	4-5	4
	Asathiosol Indigo Green S-BG	25	5	4-5	4	4-5	4
	Asathiosol Pure Blue S-GL	25	5	4-5	4-5	4-5	4-5
	Asathiosol Pure Blue S-6R	25	5	4-5	4-5	5	4-5
	Asathiosol Direct Blue S-2R	25	5	4-5	4-5	5	4
	Asathiosol Blue S-RC	25	5	4-5	4-5	4-5	3-4
	Asathiosol Blue S-BC	25	5	4-5	4-5	5	3-4
	Asathiosol Black S-H	100	5-6	5	5	5	4

Washing : JIS L-0844 A-2 (50°C, 30min.) Rubbing : JIS L-0849 (Dry)